




EXPLODED VIEW: EV 460 GENERATOR**DRAWING #: 10000032705****GROUP EV**

ITEM	PART#	QTY.	DESCRIPTION
1	10000033296	1	ENGINE GH460 HSB 2019
2	0J8254AST03	1	410 ENG MOUNTING BRKT
3	0F8186	1	ADAPTOR, ENGINE
4	0J6095	1	ALT AIR IN BELLOWS
5	0J8415	1	2 POSITION BRUSH HOLDER ASSEMBLY
6	0J9420B	1	CABLE BATT BLK #6 30.0" NEG (NOT SHOWN)
7	10000006730	1	CABLE BATT RED #6 38.5 W/BOOT (NOT SHOWN)
8	0J6938	1	CARRIER REAR BEARING MACHINED
9	0H1665	2	CLAMP BAND DIA 36-39MM
10	0G7256	1	DUCT - ALT AIR - 10" CAN - HSB
11	0C2417A	1	EARTH STRAP
12	0L5577	1	EXHAUST MANIFOLD
13	0J2350A	1	FAN EXHAUST
14	0G7283	1	FLEX PIPE
15	0G7566	1	FLEX PIPE COVER
16	0L2391	1	GASKET, EXHAUST
17	0J7062	1	LOUVER SCREEN, ALT AIR IN
18	0K0783	1	MUFFLER
19	0H1218	4	NUT FLANGE 5/16-18 NYLOK
20	0D3700	1	NUT FLANGE M6-1.0 NYLOK
21	10000034692	4	NUT FLANGE M8-1.25 NYLOK
22	0J82300ST03	1	POWERHEAD BRACKET
23	0K0468	1	ROTOR
24	G022511	4	SCREW HHC 3/8-16 X 1-1/4 G5
25	G051731	4	SCREW HHC M8-1.25 X 50 C8.8
26	G066849	2	SCREW HHTT M5 - 0.8 X 16
27	G090388	4	SCREW HHTT M6-1.0 X 12 ZINC
28	0C1069	2	SCREW HHTT M6-1.0 X 8 ZYC
29	0C5453	4	SCREW HHTT M8-1.2 X 12 BP
30	G083512	4	SCREW HHTT M8-1.2 X 16 YC
31	0J2817	1	SCREW IHHC 3/8-24 X 14.375
32	0J2816	4	SCREW IHHC M8-1.25 X 325 G8.8
33	G040976	2	SCREW SCH M8-1.25 X 20 C12.9
34	10000003925	1	STATOR
35	G029451	2.6FT	TAPE, FOAM 1/8" X 1/2"
36	0C7758	4	VIB MOUNT 1.5 X 1.38 X 5/16-18
37	0J8224	1	VIB MOUNT .50 X 1.0 X M6X1.00
38	G049451	1	WASHER FLAT .406ID X 1.62OD
39	G022131	4	WASHER FLAT 3/8-M10 ZINC
40	G022145	3	WASHER FLAT 5/16-M8 ZINC
41	G022237	5	WASHER LOCK 3/8
42	G022129	6	WASHER LOCK M8-5/16
43	0C3168	3	WASHER LOCK SPECIAL 5/16
44	0D7176	4	WASHER SELF LOCKING 1" DIA 12GA
45	077043M	3FT	CONDUIT FLEX .75" ID FR (NOT SHOWN)