



GROUP D



GROUP D



EXPLODEDVIEW: EV GH816 HSB 2019

DRAWING#: A0000347484

GROUP D

APPLICABLE TO:

ITEM	PART#	QTY.	DESCRIPTION
1	10000014943	1	WRAPPER OUTSIDE CYL 1
2	OC9764	5	SCREW HH HI-LO 1/4-15 X 3/4
3	10000041811	1	WRAPPER CENTER
4	OG0926	6	SCREW HHFCS M6-1 X 16 G8.8
5	082121C	1	CLIP-J VINYL COAT .625 ID
6	10000014974	1	WRAPPER OUTSIDE CYL 2
7	10000009751	1	CAP OIL FILL ASSY M30
8	10000029570	1	HOSE BREATHER HSB 2019
9	OG0767B	2	SPARK PLUG GAP 0.020"
10	OF2094	2	SCREW PPHMS M3-0.5 X 6
11	10000024110	1	THERMAL SWITCH 310 F NC
12	070185E	1	OIL FILTER 90 LOGO ORNG-CAN
13	OL2917D	1	LOW OIL PRES SWITCH 10 PSI NO
14	10000034692	4	NUT HEX FLANGE M8-1.25 LOCK NYLON
15	OL6347	1	BARB STR SAE 3/8NPT X 3/8 ST-Z
16	OG3662B	5	CLAMP HOSE STEPLESS 18.5
17	OH8131	1	ASSY HOSE OIL DRAIN 16"LG ORG
18	10000019150	1	ST03 MOUNTING BRKT HSB 816/999 ENG
19	G022145	3	WASHER FLAT 5/16-M8 STEEL ZINC
20	G051731	4	SCREW HHC M8-1.25 X 50 C8.8
21	OC3168	1	WASHER LOCK SPECIAL 5/16
22	10000022810	1	KEY WOODRUFF 5 X 22
23	10000014973	1	BLOWER HOUSING WITH OIL COOLER
	10000043430	1	BLOWER HOUSING NO OIL COOLER
24	OL6345	2	BARB STR SAE 1/4NPT X 3/8 ST-Z
25	OF0452C	2	HOSE 3/8" 300DEG 6" LONG OIL
26	OC9764	1	SCREW HH HI-LO 1/4-15 X 3/4
27	10000037763	1	OIL COOLER 300 BTU HOOKS
28	A0000513161	1	FLYWHEEL ASSY WITH GEAR 255MM 33 DEG 5MM KEY
29	OC3031	1	FAN FLYWHEEL NYLON GTV990
30	OC3032	1	PLATE, FAN GV-990
31	OH4957	2	SCREW HHFCS M8-1.25 X 10 C8.8
32	OC3033	1	WASHER BELLEVILLE 25MM BOLT
33	OC3034	1	NUT HEX M24-2.0 G8 YEL CHR
34	10000014972	1	COVER BLOWER HOUSING WITH OIL COOLER
	10000043421	1	COVER BLOWERHOUSING NO OIL COOLER
35	10000029070	1	BLWR HSG PLUG
36	OK1280	1	ASSY GROUNDING WIRE 2013 HSB
37	10000004931	1	ASSY IGN COIL R128.3 X 390 NO GROM
38	10000004916	1	ASSY IGN COIL R128.3 X 335 NO GROM
39	OJ9420B	1	CABLE BATT BLK #6 30.0 NEG
40	A0000501971	1	STARTER MOTOR GEAR REDUCED 1KW
41	G022129	2	WASHER LOCK SPRING 5/16 ZC
42	G061906	2	SCREW HHC M8-1.25 X 85 C8.8
43	10000014766	1	MANIFOLD INT HSB 2X MCHND
44	OG3730A	4	SCREW SHC M8-1.25 X 30 G8.8 SEMS
45	10000014758	2	GASKET INTAKE MANIFOLD
46	OF6510	9	SCREW HHFC M8-1.25 X 40 C10.9
47	10000009733	1	GEAR COVER 35MM ASSY COOLER
	10000022900	1	GEAR COVER 35mm ASSY NO COOLER
48	078699B	2	SLEEVE DOWEL PIN 12 DIA.
49	10000029131	1	CAMSHAFT-MACHINED 19.8 LIFT
50	A0001193894	1	PUMP OIL ASSY
51	OG6431	2	SCREW, SOCKET HEAD CAP M6-1.0 SEMS
52	10000008403	2	RING PISTON TOP DIA 85
53	10000008389	2	RING PISTON 2ND DIA 85
54	10000008394	4	RING PISTON OIL RAIL DIA 85
55	10000008430	2	RING PISTON OIL SPACER DIA 85
56	OL6110	1	SCREW SHC M6-1.0 X 20 C8.8
57	G071983	4	RETAINER PISTON PIN 20
58	10000037649	1	ASSY OIL PICK-UP PLASTIC
59	OE3812	2	SEAL D 35 X 48.2 VITON
60	OK6397	2	WRIST PIN 999 20X12X49
61	10000008954	2	ASSY CONNECTING ROD 112.7
62	OK0710	2	O-RING 1-3/4 X 1/16 VITON 031

EXPLODEDVIEW: EV GH816 HSB 2019**DRAWING#: A0000347484****GROUP D****APPLICABLE TO:**

ITEM	PART#	QTY.	DESCRIPTION
63	10000014512	2	ASSY PISTON FLAT TOP 85 DIA 8.5 CR
64	10000016990	1	ASSY CRANKSHAFT 36 MM HSB TAPER
65	10000018344	1	CC 85MM MACHINED W/TAPPER PLUGS
66	10000033011	2	GASKET HEAD 85MM
67	078699C	4	SLEEVE DOWEL PIN DIA.14
68	10000014751	2	VALVE INTAKE 34 MM
69	10000014770	2	VALVE EXHAUST 27 MM
70	10000014726	1	ASSY HEAD CYL #2 85MM
71	10000023678	10	SCREW HWH SEMS M10-1.5 X 100
72	10000014772	4	HLA ASSEMBLY 15.6MM DIA
73	10000014780	4	PUSHROD
74	10000027581	2	PLATE PUSHROD GUIDE STL
75	0C5371	4	WASHER VALVE SPRING
76	10000021593	4	VALVE STEM SEAL 6 X 12.7
77	0L5489	4	SPRING VALVE GT999
78	0D2274	4	RETAINER,VALVE SPRING
79	G086515	8	KEEPER,VLV SPRING
80	10000008511	4	ROCKER ARM
81	10000027536	4	STUD ROCKER BALL
82	0J4967	2	SCREW HHFC M5-0.8 X 12
83	10000045274	1	ASSY BREATHER PLATE
84	10000045265	1	GASKET BREATHER
85	10000040133	1	COALESCING MEDIA
86	10000014927	2	GASKET ROCKER COVER 85MM
87	G080318	12	SCREW HHFC M6-1.0 X 25 FTH G8
88	10000014960	1	ROCKER COVER 85MM GPB W/BREATHER MCHND
89	A0002291953	2	BRACKET LIFT V-TWIN
90	10000009595	1	ASSY HEAD CYL #1 85MM
91	10000034577	1	ROCKER COVER 85MM GPB NO BREATHER MCHND
92	10000014502	2	PISTON FLAT TOP 85 DIA 8.5 CR