GP6500

GENERAC®

GP SERIES
Portable Generator

FEATURES

Model G007672-3 UPC: 696471108255
(49 State)


- **Generac's 389cc OHV engine** with splash lubrication provides a long engine life.
- **Large-capacity steel fuel tank** with incorporated fuel gauge provides durability and up to a 11.5 hour run-time when 50% of power is being used.
- **1 ¼" steel-tube cradle** for added durability and strength.
- **Heavy-duty, never-flat wheels** allow for easy portability.
- **Fold-down handle** for sturdy portability and compact storage.
- **COsense® Technology** – STOPS, ALERTS, SAVES. Powerful protection against hazardous carbon monoxide.
- **Low-oil level shutdown** automatically safeguards engine from damage.
- **Hour Meter** tracks maintenance intervals.
- **20ft 20A Generator Cord Included** – Plug in more devices with the multi-outlet generator cord.
- **HomeLink™** manual transfer switch compatible.



Photograph may not represent actual content.

AC Rated Output Running Watts 6500
AC Maximum Output Starting Watts 8125

CONTROL PANEL



USA ENGINEERED


SPECIFICATIONS

Product Series	GP6500
Model (Configuration)	7672-3 (49-State)
AC Rated Output Running Watts	6500
AC Maximum Output Starting Watts	8125
Rated AC Voltage	120/240 VAC
Rated AC Frequency	60 Hz
Rated 120/240 VAC Amperage	54.2 / 27.0
Engine Displacement	389cc
Engine Type	OHV
Engine RPM	3600
Recommended Oil	10W-30 / SAE 30
Oil Capacity qt (L)	1.06 (1.0)
Lubrication Method	Spash
Automatic Voltage Regulation (AVR)	Yes
Choke Location	On Engine
Fuel Shut Off	On Fuel Tank
Starting Method	Recoil Pull Start

Low Oil Shutdown	Yes
Neutral Bonded to Ground	Yes
Start Switch Type	On / Off
Start Switch Location	On Control Panel
Fuel Gauge	Yes
Fuel Tank Capacity Gal (L)	7.9 (29.9)
Run Time at 25% (Hours)	16.5
Run Time at 50% (Hours)	11.5
Handle Style	Dual Grip, Single Folding with Lock Pin
Wheel Type	9.5" Never Flat
Generator Cord Included	20ft / 20A Outdoor, Multi-Outlet with Lighted Power Indicator
Warranty- Commercial	2 Year Limited
Warranty- Residential	3 Year Limited
Included	20ft generator cord, engine oil, oil funnel, handle & wheel kit, owner's manual

DIMENSIONS AND WEIGHTS

Length in (mm)	27.2 (692)
Width in (mm)	27 (684)
Height in (mm)	26.5 (674)
Extended Length in (mm)	45.3 (1151)
Carton Length in (mm)	28.3 (720)
Carton Width in (mm)	21.7 (550)
Carton Height in (mm)	28 (710)
Unit Weight lbs (kg)	172 (78)
Shipping Weight lbs (kg)	196 (88.9)



©2026 Generac Power Systems, Inc. All rights reserved. All specifications are subject to change without notice.
Part No. 10000032664
Rev. F 7/14/2026