

GP6500E DF

GP SERIES Portable Generator

Model G0081520 UPC: 696471104653
(50-State)


Features

- **Dual Fuel** – Runs on gasoline or liquid propane fuel.
- **Fuel source selector** allows the unit to switch seamlessly between fuel types to prevent unit shutdown.
- **13-Hour Runtime** when running on gasoline and 6-Hour Runtime on 20lb LP tank when 50% of power is being used.
- **Easy-to-Use Electric Start** – Rocker switch provides reliable and hassle-free start ups (Battery included).
- **Fuel-Efficient OHV Engine** – 340cc OHV engine with EFI technology optimizes fuel efficiency and requires less maintenance.
- **Handle & Wheel Kit** – Ergonomic handle and never-flat wheel kit included for portability.
- **1 1/4" steel-tube cradle** for added durability and strength.
- **Covered outlets** provide added protection from the environment and rugged working conditions.
- **Low-oil level shutdown** automatically safeguards engine from damage.
- **COsense® Technology** – STOPS, ALERTS, SAVES. Powerful protection against hazardous carbon monoxide.
- **HomeLink™ Manual Transfer Switch compatible** designed to work with HomeLink™ manual transfer switches for safe home backup power.



Running Watts 6500 (Gas) 5850 (LP)
Starting Watts 8125 (Gas) 7300 (LP)

Control Panel



GP6500E DF

Specifications

Product Series	GP6500E DF
Model Number	8152-0
Configuration	50-State
AC Rated Output Running Watts	6500 (Gas) / 5850 (LP)
AC Maximum Output Starting Watts	8125 (Gas) / 7300 (LP)
Rated AC Voltage	120/240 VAC
Rated AC Frequency	60 Hz
Rated 120/240 VAC Amperage	27.1 / 54.2 (Gas) - 48.8 / 24.4 (LP)
Engine Displacement	340cc
Engine Type	OHV
Engine RPM	3600
Recommended Oil	10W-30 / SAE 30
Oil Capacity qt (L)	1.06 (1.0)
Lubrication Method	Splash
Digital Automatic Voltage Regulation (DAVR)	Yes
Starting Method	Electric Start / Recoil Pull Start
Battery Included	Yes
Battery Type	Lead Acid (12V DC, 9Ah)

Battery Part No.	A0006353770
Battery Dimensions	5.94" x 2.56" x 3.70"
Low Oil Shutdown	Yes
Neutral Bonded to Ground	Yes
Start Switch Type	Off/Run/Start
Start Switch Location	On Control Panel
Fuel Gauge	Yes
Fuel Tank Capacity gal (L)	7.5 (28.4)
Run Time at 25% (Hours)	16 (Gas) / 7 (LP)
Run Time at 50% (Hours)	13 (Gas) / 6 (LP)
Handle Style	Dual Grip, Single Folding with Lock Pin
Wheel Type	9.5" Never Flat
Warranty- Residential	3 Year Limited
Warranty- Commercial	2 Year Limited
Included	Engine oil, handle & wheel kit, battery, owner's manual, LP hose with primary regulator to connect to 20lb LP tank

Dimensions and Weights

Length in (mm)	30.2 (767.1)
Width in (mm)	27.2 (690.9)
Height in (mm)	27 (685.8)
Extended Length in (mm)	44 (1140)
Carton Length in (mm)	28.6 (726.4)
Carton Width in (mm)	21.7 (551.2)
Carton Height in (mm)	28 (711.2)
Unit Weight lbs (kg)	175 (79.4)
Shipping Weight lbs (kg)	191 (86.6)

