


GROUPE



EXPLODEDVIEW: EV FUEL SYSTEM G4.5L TURBO C3**DRAWING#: A0000282715****GROUP E****APPLICABLE TO:**

ITEM	PART#	QTY.	DESCRIPTION
1	0L1422	1	ELBOW 45D 1-1/4 NPT BLK IRON
2	G035586	2	CLAMP HOSE #20 .87-1.75
3	G057434	1	HOSE 1.25 ID LP & NG (19"LG)
4	G070303	2	BARBED STRAIGHT 1.25 NPT X 1.25
5	G030131	1	ELBOW 90D 1-1/4NPT
6	0K9049	2	NIPPLE PIPE 1-1/4 NPT X 2 ZINC
7	0E0694	2	ASSY NATGAS FUEL SOLENOID 24V
8	G039414	8	SCREW HHC M8-1.25 X 35 C8.8
9	G045771	8	NUT HEX M8-1.25 G8 CLEAR ZINC
10	10000018175	1	SENSOR LOW PRESSURE 4KPA
11	10000039804	1	BRACKET-PRESSURE SENSOR
12	A0000263955	1	FITTING 1/8" M NPT X 10.4 MM DIA
13	G022129	12	WASHER LOCK SPRING 5/16 ZC
14	G064346	1	PIPE TEE 1-1/4 NPT
15	A0000379506	2	ST03 BRKT FUEL VLV FRAME G4.5L G26 ASCO
16	A0000139077	1	SWITCH PRESSURE GAS 3.1" RISE
17	0E7162	1	BSHG RDCR HEX 1-1/4 X 1/4FNPT
18	G022145	20	WASHER FLAT 5/16-M8 STEEL ZINC
(2)19	A0000271134	2	HARN JUMPER FUEL SOLENOID (NOT SHOWN)
20	G043107	4	SCREW HHC M8-1.25 X 25 C8.8
21	0L5885	1	PLUG PLASTIC 1.25 TAPERED CAP
22	055945A	1	O-RING - DBL GAS SHUTOFF VALVE
(1)23	A0000215896	1	HARN FUEL SYS G4.5L G26 (NOT SHOWN)
24	10000035712	1	FITTING-1-1/4" M NPT x 1-5/8" F JIC ELBOW
25	G029453	1	PIPE TEE 1/4 NPT
26	G035579	1	BSHG RDCR HEX 1/4 TO 1/8
27	0K2340	1	PLUG PRESSURE GAUGE 1/4" NPT
28	0K3795	1	HANG TAG FUEL PRESSURE TEST POINT
29	0K6367	1	NIPPLE HEX 1/4-18 NPT STL/ZC
30	A0000156899	REF	GROMMET FULE LINE 1-1/4

NOTES (UNLESS OTHERWISE SPECIFIED):

(1) I/N 23 CONNECTS I/N 16 AND I/N 7.

(2) ONE JUMPER USED FOR EACH I/N 7 VALVE AS INTERFACE TO HARNESS.