




SH	1/1	REV	D	WINDCHILL VERSION	D.2	
SYM	ITEM #	PART #	QTY	DESCRIPTION		
	1	0L2910	1	XFRSW HSB 100A 2P 250V		
	2	G074908	6	SCREW HHTT M5-0.8 X 10 BP		
	3	077033	6	LUG SLDLSS 1/0-#14X9/16 AL/CU		
	4	022152	6	WASHER LOCK SPRING #10 ZC		
	5	036933	6	SCREW PPHM #10-32 X 3/8		
	6	10000009445	4	90 DEGREE STRAIGHT SPADE CONNECTOR		
	7	G074138	1	LUG DIS QK NI-S 10X45 DEG BR/T		
*	8	0L1934B	1	HARNS, LC INT CONN, 100A		
*	9	0L1934C	1	HARNS, LC INT CONN, 100A		
	10	0L0288	1	16 CIR L/CNTR 125A/240 SIEMS		
	11	G066849	2	SCREW HHTT M5-0.8 X 16		
	12	10000000817	1	ALOR ENCLOSURE 200A SE XFRSW		
	13	10000000830	1	ALOR COVER,200A SE XFRSW		
	14	10000019615	1	INSIDE COVER 200A 16 CIRCUIT		
	15	0L06990GS0R	1	BRKT, BARRIER, 100A NEMA3R		
	16	10000019719	1	SUBPLATE GTS LOAD CENTER		
	17	0G8411	4	NUT HEX FLANGE WHIZ 1/4-20		
	18	085889	1	NUT HEX 1/4-20 SS		
	19	10000004363	1	FUSED CONTROL MODULE		
	20	10000005117	1	FUSE 6.3A 250VAC 5mmX20mm		
*	21	10000005872	1	HARNESS 100/200A TS		
	22	0E6155	1	PIN ARM EXTENDER		
	23	0K8254	1	U-CLIP ADHESIVE		
	24	10000005894	1	DECAL TEST SEQUENCE RTG 3R		
	25	10000008602	1	DECAL WCR NEC COMPLIANCE		
	26	10000037322	1	DECAL PROP 65 EN/SP/FR		
	27	067210A	1	DECAL GROUND LUG		
	28	0E3484	1	DECAL WARN MANUAL OPER HANDLE		
	29	0G3259	1	DECAL TERMINAL SHOCK HZD BI		
	30	0G3274	1	DECAL LIVE CIRCUIT ENG/FRN/SPN		
**	31	0J0894	1	DECAL LC 16 CIRC. GENERAC		
**	32	0K1098	1	DECAL RTS TRANSFER SW GENERAC		
	33	0L3546	1	DATA DECAL PANEL BOARD		
	34	0L6700	1	SCREW THUMB 1/4-20 X 1/2 KNURL		

*-NOT SHOWN ON THIS ASSEMBLY
**-DECALS PER MODEL SEE TABLE

REFERENCE DRAWINGS

10000018987 SCHEMATIC DIAGRAM
10000019053 WIRING DIAGRAM
0K1846 CARTON 30'5 X 14'2 X 7

PART NUMBER	DESCRIPTION	ITEM #32	ITEM #33	MANUAL	WARRANTY
10000010418	RTG LCTR ASSY 16 CIR-GENERAC	0J0894	0K1098	10000012410	0K9470
10000010473	RTG LCTR ASSY 16 CIR-HONEYWELL	10000003120	0K1274	10000019143	0K3103
10000012054	T/S 16CKT. LC 100A NEMA3R GEN	0J0894	0K1098	10000012410	0K9470
10000019165	T/S 16CKT. LC 100A NEMA3R HNYWL	10000003120	0K1274	10000019143	0K3103
10000023713	T/S 16CKT. LC 100A NEMA3R DR	10000029191	10000023086	10000024114	10000023720
10000023730	T/S 16CKT. LC 100A NEMA3R PWRM	10000029191	10000023483	10000024115	10000028401

GENERAL TOLERANCES UNLESS NOTED		THIRD ANGLE PROJECTION	
ALL XX = ± 0.4 MM	XXX = ± 0.4 MM		
XX-XX = ± 0.15 MM			
ALL ANG = ± 1°			
INTERPRET DIM AND TOL PER ASME Y14.5M-1994			

GENERAC POWER SYSTEMS OWNS THE COPYRIGHT OF THIS DRAWING WHICH IS SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSES OTHER THAN FOR WHICH IT IS SUPPLIED WITHOUT THE EXPRESS WRITTEN CONSENT OF GENERAC POWER SYSTEMS.
© GENERAC POWER SYSTEMS 2010

ELECTRONICALLY APPROVED
INSIDE WINDCHILL

TITLE				LOAD CENTER ASS'Y 16 CIRC. 3R ENCLOSURE			
ISSUE DATE:							
SIZE	CAGE NO	DWG NO	REV				
D	N/A	10000010468	D				
SCALE	0.400	WT-KG	67913.366	SHEET	1	of 1	