

GP3600

GP3600 GP Series Portable Generator

FEATURES

- Generac's 212cc OHV engine with splash lubrication provides a long engine life.
- Large-capacity steel fuel tank with incorporated fuel gauge provides durability and 9 hour runtime when 50% power is being used.
- 1-1/4" Hardened Steel Tube Cradle for added strength and durability.
- Heavy-duty, never-flat wheels for reliable portability (wheel kit included).
- Fold down handle for sturdy portability and compact storage (handle included).
- COsense® TECHNOLOGY – STOPS, ALERTS, SAVES. Powerful protection from hazardous carbon monoxide.
- Low-oil level shutdown automatically safeguards engine from damage.
- Hour Meter tracks maintenance intervals.

*Increases electrical current upon demand above rated output when starting electric motors.


Model 7721-2 UPC 696471108606 (49ST/CSA)



Photograph may not represent actual content.

AC Rated Output Running Watts 3600
AC Maximum Output Starting Watts 4500

CONTROL PANEL



SPECIFICATIONS

Product Series	GP3600
Model Configuration	7721-2 (49ST-CSA)
AC Rated Output Running Watts	3600
AC Maximum Output Starting Watts	4500
Rated AC Voltage	120 VAC
Rated AC Frequency	60 Hz
Rated 120 VAC Amperage	30A
Engine Displacement	212cc
Engine Type	OHV
Engine RPM	3600
Recommended Oil	10W-30 / SAE 30
Oil Capacity qt (L)	0.63 (0.6)
Lubrication Method	Splash
Automatic Voltage Regulation (AVR)	Yes
Starting Method	Recoil Pull Start
Low Oil Shutdown Method	Yes
Bonded Neutral	Yes

Start Switch Type	On/Off
Start Switch Location	On Control Panel
Fuel Gauge	Yes
Fuel Tank Capacity Gal (L)	3.7 (14)
Run Time at 50% (Hours)	9.3
Handle Style	Single Folding
Wheel Type	8 in. Never Flat
Warranty- Residential	3 Year Limited
Warranty- Commercial	2 Year Limited
Included	Engine oil, oil funnel, handle and wheel kit, and Owner's manual

DIMENSIONS AND WEIGHTS

Length in (mm)	24 (610)
Width in (mm)	22.5 (570.5)
Height in (mm)	21.3 (541.5)
Extended Length in (mm)	36.5 (924)
Carton Length in (mm)	27.2 (690)
Carton Width in (mm)	17.9 (455)
Carton Height in (mm)	19.7 (500)
Unit Weight lbs (kg)	105 (47.6)
Shipping Weight lbs (kg)	112 (50.8)

