

212cc Gasoline Engine (G19)


Engine Parts Manual

 WARNING

Operating, servicing and maintaining this equipment can expose you to chemicals including engine exhaust, carbon monoxide, phthalates, and lead, which are known to the State of California to cause cancer and birth defects or other reproductive harm. To minimize exposure, avoid breathing exhaust, do not idle the engine except as necessary, service your equipment in a well-ventilated area and wear gloves or wash your hands frequently when servicing your equipment. For more information go to www.P65Warnings.ca.gov.

(000393)

The information in this manual is accurate based on products produced at the time of publication. The manufacturer reserves the right to make technical updates, corrections, and product revisions at any time without notice.



005965

ITEM	PART NO.	DESCRIPTION	QTY
1	0G84420217	FLANGED BOLT (M6X14MM)	6
2	0J88870104	VALVE COVER	1
3	0J88870108	BREATHER CHAMBER FILTER	1
4	0J88870107	BREATHER CHAMBER GASKET	1
5	10000021973	FLANGE BOLT (M5X10MM)	2
6	0J88870106	BREATHER CHAMBER CAP	1
7	10000023964	BREATHER TUBE	1
8	10000022119	SHROUD	1
9	0J88870103	VALVE COVER GASKET	1
10	0J35220158	CYLINDER HEAD BOLT (M8X60)	4
11	0J00620106	SPARK PLUG	1
12	0J88870101	CYLINDER HEAD ASSEMBLY	1
13	0K10430117	ROCKER ARM SHAFT CIRCLIP	2
14	0J88870120	ROCKER ARM ASSEMBLY	2
15	0J35230114	VALVE ROTATOR	2
16	0J35220118	VALVE SPRING SEAT	2
17	0J35220117	VALVE SPRING	2
18	0J35230140	INTAKE AND EXHAUST VALVE SET	1
19	0J88870119	VALVE ROCKER SHAFT	2
20	0J88870121	PUSHROD	2
21	0J35220122	VALVE TAPPET	2
22	0J35220119	VALVE GUIDE SEAL	1
23	0G84420210	EXHAUST STUD (M8X34MM)	2
24	0J47870111	INTAKE STUD (M6X96MM)	2
25	0J35220128	INSULATOR GASKET	1
26	10000024001	CARBURETOR SPACER	1
27	0J35220127	CARBURETOR GASKET	1
28	10000023984	MOTOR PLATE	1
29	0J86620110	SCREW (M4X12MM)	2
30	10000024003	THROTTLE CONTROL MOTOR	1
31	10000023977	SCREW (M3X5MM)	2

ITEM	PART NO.	DESCRIPTION	QTY
32	10000024014	CARBURETOR	1
33	0J88870130	CLAMP COLLAR	1
34	10000022158	FUEL HOSE	1
35	10000024004	CARBURETOR GASKET	1
36	10000023993	CHOKE BRACKET	1
37	10000024020	CARBURETOR GASKET	1
38	10000021871	FLANGE NUT (M6)	2
39	10000024021	AIR CLEANER ASSEMBLY	1
40	Not Available	PISTON RING SET	1
41	Not Available	PISTON	1
42	0J47870131	CONNECTING ROD ASSEMBLY	1
43	Not Available	PISTON PIN	1
44	Not Available	PISTON PIN CIRCLIP	2
45	Not Available	FLANGE BOLT (M8X32MM)	6
46	0J35220166	OIL SEAL	2
47	Not Available	CRANKCASE COVER	1
48	Not Available	PLATE	1
49	Not Available	FLANGE BOLT (M6X10MM)	2
50	Not Available	RADIAL BALL BEARING 6205	2
51	Not Available	OIL LEVEL SWITCH ASSEMBLY	1
52	Not Available	CRANKCASE COVER GASKET	1
53	Not Available	DOWEL PIN	2
54	Not Available	CRANKSHAFT ASSEMBLY	1
55	Not Available	CAMSHAFT ASSEMBLY	1
56	0K10430110	CYLINDER HEAD GASKET	1
57	0J35220165	DOWEL PIN	2
58	10000023988	DIPSTICK ASSEMBLY	1
59	0J35220111	DRAIN PLUG BOLT	1
60	0J35220164	DRAIN PLUG WASHER	1
61	Not Available	CRANKCASE ASSEMBLY	1
62	10000022097	PLATE	1
63	0G84420228	DOWEL PIN	2
64	10000022075	IGNITION COIL	1
65	0G84420268	FLANGE BOLT (M6X25MM)	2

ITEM	PART NO.	DESCRIPTION	QTY
66	10000023997	BOTTOM GUARD SHIELD	1
67	10000021809	SCREW (ST4.0 X15MM)	2
68	10000024033	FLANGED BOLT (M5X8MM)	2
69	10000017391	ALTERNATOR	1
70	10000024052	WASHERS	4
71	10000022204	SOCKET HEAD SCREW	4
72	10000022168	FLAT WASHER	1
73	10000024053	ROTOR BOLT (M8X28MM)	1
74	10000022166	COOLING FAN	1
75	10000022203	STARTING PULLEY	1
76	10000022194	FLANGED BOLT (M6X16MM)	8
77	10000022195	FAN COVER WITH RECOIL	1
78	0J35250337	CABLE CLEAT	1
79	10000024100	SCREW (M5X12MM)	1
80	0G84420194	FLANGED BOLT (M6X12)	2

Part No. 10000017722Rev. A 03/29/2018
 ©2018 Generac Power Systems, Inc.
 All rights reserved
 Specifications are subject to change without notice.
 No reproduction allowed in any form without prior written
 consent from Generac Power Systems, Inc.



Generac Power Systems, Inc.
 S45 W29290 Hwy. 59
 Waukesha, WI 53189
 1-888-GENERAC (1-888-436-3722)
www.generac.com