


Parts Manual

60 Hz Air-Cooled Generators

Model: 14 kW G0072580 & G0073230



SAVE THIS MANUAL FOR FUTURE REFERENCE

 WARNING

CANCER AND REPRODUCTIVE HARM
www.p65warnings.ca.gov

(P000393)

Table of Contents


<i>Common Replacement Parts</i>	<i>4</i>
<i>ENCLOSURE AND DECALS.....</i>	<i>6</i>
<i>TOP LEVEL ENG, FUEL, EXHAUST, ALTERNATOR.....</i>	<i>10</i>
<i>ENGINE SUBCOMPONENTS</i>	<i>14</i>
<i>CONTROL SYSTEM AND LOOSE PARTS</i>	<i>16</i>

Common Replacement Parts

Part Number	Part Description	QTY	Remarks
A0003637864	SPARK PLUG GENERAC GAP: 0.020"	2 ea	
G0072160	KIT MAINTENANCE 13-28 KW 816/817/997CC	1 ea	
A0009643725	OIL, BREAK-IN 12QT CASE SAE 5W-30	2.5 qt	Available in 12 qt case
070185E	OIL FILTER 90 LOGO ORNG-CAN	1 ea	
0J8478S	FILTER AIR ELEMENT PRE-BOX	1 ea	
0G66240KEY	KEY FOR LOCK 0G6624	1 ea	Comes with A0007504626
G0099180	TOUCH-UP PAINT METRO GRAY	1 ea	
A0001412864	OIL-5W-20 FULL SYN ENG (CASE /12 QTS)	2.5 qt	

This page intentionally left blank.

ENCLOSURE AND DECALS



ENCLOSURE AND DECALS (continued)


Item	Part Number	Description	Qty.	Remarks
1	A0007645935	KIT - MOUNTING FOOT	4	
2	A0004161392	SCREW HH SERR FLG M6-1.0 X 12 ZP	21	
3	A0002494196	SCREW TORX BTN M6-1.0 X 12 ZK	5	
4	A0007645939	KIT - ROOF REPLACEMENT	1	Item 35 is included with item 4
5	A0008082540	KIT - ROOF HINGE	1	
6	A0006008751	STRUT GAS ROOF SUPPORT HSB	1	
7	A0007645941	KIT - BACK PANEL	1	
8	A0004382392	SCREW HH HI-LO M6.3 X 16MM	8	
9	A0007887150	KIT - COMMON DECALS	1	
10	A0004201681	GN57 BASE PANEL HSB	1	
11	A0006793040	MOUNTING PAD ASSY HSB PRIME RESIN	1	
12	A0009134973	KIT-EXHAUST PANEL NESTED	1	
13	A0007649792	KIT - INSULATION	1	
14	A0004330551	ST03 PANEL EXHAUST FRONT WIDE B	1	
15	A0006060342	ST03 WELDMNT PANEL EXHAUST TOP STRUT	1	
16	A0009134974	KIT-FRONT PANEL NESTED	1	
17	A0007504626	KIT - LOCK REPLACEMENT	1	
18	A0005204186	SCREW TORX CUSTOM HI-LO STL ZP	7	
19	A0002010098	BEZEL LOCK HSB BLACK	1	
20	A0007647638	KIT - GROMMETS	1	
21	10000022416	SCREW HHFC M6-1.0 X 16 C8.8	1	
22	A0009134972	KIT-INTAKE PANEL NESTED	1	
23	A0005125723	ST03 PNL TOP CUSTOMER CXN 60HZ 1PH	1	
24	A0006524367	ST11 ASSY PNL BTTM CUSTOMER CXN EXTRUDES	1	
25	A0007358752	ST03 WLDMT PANEL SIDE CUST CONNECTION	1	
26	A0004543048	ST03 PANEL ENGINE DIVIDER HSB	1	
27	A0001055848	BRACKET DUAL RELAY	1	
28	A0006634851	BAFFLE ENGINE FAN HSB	1	
29	0G7717	SCREW HH HI-LO M6.3 X 10MM	2	
30	A0004520123	GASKET EXHAUST PANEL HSB	1	
31	A0007205196	GASKET FRONT PANEL NESTED BOTTOM HSB	1	
32	A0006523228	GASKET END PANEL FRONT SIDES HSB	2	
33	A0008186350	GASKET EXTRUDED TRIM RIBBED UL	2	
34	A0004330540	ST03 WLDMNT PNL EXH DIVIDER 816/254 C	1	
35	A0001380433	GASKET EXTRUDED TRIM UL	10.8 ft	Item 35 is included with item 4
36	A0004332725	HARN GND LEAD AC HSB 8AWG	1	Item not shown

ENCLOSURE AND DECALS (continued)

Item	Part Number	Description	Qty.	Remarks
37	A0010204639	KIT - LOCK ASSY	1	
38	A0001034596	FOAM ENGINE DIVIDER HSB 816/999	1	

This page intentionally left blank.

TOP LEVEL ENG, FUEL, EXHAUST, ALTERNATOR



TOP LEVEL ENG, FUEL, EXHAUST, ALTERNATOR (continued)


Item	Part Number	Description	Qty.	Remarks
1	0G7408	SCREW IHHC 3/8-24 X 17.50 G8	1	Item 1 is included with item 37
2	A0007649832	KIT - EXHAUST FAN	1	
3	A0004533859	SCREW HHFC M8-1.25 X 393 C8.8	4	
4	A0007649806	KIT - BRUSH ASSY	1	
5	A0004332760	254 REAR BEARING CARRIER MACHINED	1	
6	A0004736528	RTR 10 2P 14 AD1 HSB 2023	1	
7	A0004123468	STR 10 2P 14 AD1 HSB 2023	1	
8	A0007649805	KIT - ALT HARN TERMINAL ASSY	1	
9	A0007649808	KIT-ALT EXH DUCT	1	
10	A0002500762	BELLOWS ALT INTAKE HSB	1	
11	A0008286303	KIT-MUFFLER	1	Includes 1x item 13 for reinstallation
12	0J7240	CLAMP BAND DIA 42.7-46.7MM	2	
13	A0007325187	KIT - EXHAUST FLEX PIPE	1	This item is not reusable and must be replaced upon removal
14	A0007325192	KIT - FLEX PIPE COVER	1	
15	A0007648331	KIT - EXHAUST MANIFOLD	1	Includes 1x item 13 for reinstallation
16	A0002057615	SENSOR OXYGEN SWITCHING	1	
17	A0007674973	KIT-IGN COIL ASSY	2	
18	A0007674971	KIT-INTAKE MANIFOLD 817	1	
19	A0007887144	KIT - SEDIMENT TRAP	1	
20	A0006853913	O-RING 29.82 ID X 2.62MM	1	
21	A0007887145	KIT - FUEL LINE	1	
22	A0007648329	KIT - ETC / MIXER	1	
23	A0007649029	KIT - MIXER PRES SENSOR	1	
24	A0007649020	KIT - AIRBOX REPLACEMENT	1	
25	0J8478	FILTER AIR ELEMENT 236X139X37	1	
26	A0001455554	BELLOWS 816/999 ENGINE INTAKE HSB	1	
27	A0006060389	GASKET-MIXER/ETC TO INTAKE	1	
28	10000014758	GASKET INTAKE MANIFOLD	2	
29	A0002872809	T-BOLT HOSE CLAMP 28-32MM	2	
30	0C4138	GASKET EXHAUST PORT	2	
31	A0009318347	KIT-ENGINE REPLACEMENT 14-18KW ACHSB	1	Contains items 13, 28, 27, 30, and 36, and intends to capture all parts needed to reinstall the replacement engine
32	A0007647636	KIT - BATTERY LEADS	1	
33	A0007647702	KIT - REGULATOR ASSY	1	

TOP LEVEL ENG, FUEL, EXHAUST, ALTERNATOR (continued)

Item	Part Number	Description	Qty.	Remarks
34	0L4836A	FUEL LINE FLEX 3/4 NO PVC	1	
35	A0007887141	KIT - FUEL SHUTOFF	1	
36	A0001227957	O-RING 61.60 ID X 2.62MM ISO-143	1	
37	A0008625460	KIT - ALTERNATOR ASSEMBLY	1	Item 1 is included with item 37

This page intentionally left blank.


ENGINE SUBCOMPONENTS



ENGINE SUBCOMPONENTS (continued)

Item	Part Number	Description	Qty.	Remarks
1	A0003637864	SPARK PLUG GENERAC GAP: 0.020"	2	
2	A0007675010	KIT-STARTER MOTOR	1	
3	070185E	OIL FILTER 90 LOGO ORNG-CAN	1	
4	10000022810	KEY WOODRUFF 5 X 22	1	
5	A0007674977	KIT-ROCKER COVER W BREATHER	1	
6	10000014927	GASKET ROCKER COVER 85MM	2	
7	10000033011	GASKET HEAD 85MM	2	
8	0E3812	SEAL D 35 X 48.2 VITON	2	
9	0L2917D	LOW OIL PRES SWITCH 10 PSI NO	1	
10	A0007674974	KIT-ROCKER COVER WO BREATHER	1	
11	A0007674843	KIT-FRONT COVER	1	
12	10000022639	FLYWHEEL/RING GEAR 255MM FOR EFI	1	
13	A0007676172	KIT-FAN	1	
14	A0007674976	KIT-CYLINDER HEAD #1 817	1	
15	A0008095272	KIT-SPRING REPLACEMENT	4	
16	A0008095580	KIT-ROCKER ARM AND STUD	4	
17	A0007676180	KIT-HEAD TEMP SENSOR	1	
18	A0007674967	KIT-CYLINDER HEAD #2 817	1	
19	A0007674961	KIT-OIL FLOAT ASSY	1	
20	A0007676175	KIT-OIL DRAIN ASSY	1	
21	A0007674963	KIT-CRANK POSITION SENSOR 817	1	
22	A0007674953	KIT-BATTERY CHARGE STATOR	1	
23	10000009751	CAP OIL FILL ASSY M30	1	
24	G022129	WASHER LOCK M8-5/16	2	
25	G061906	SCREW HHC M8-1.25 X 85 C8.8	2	

CONTROL SYSTEM AND LOOSE PARTS



CONTROL SYSTEM AND LOOSE PARTS (continued)

Item	Part Number	Description	Qty.	Remarks
1	A0000697882	ENGINE CONTROL MODULE-46 PIN GASEOUS	1	
2	0E7886F	CB 0060A 2P 240V S BQ2 LB	1	
3	0H3535	NUT FLANGE M5-0.8 NYLOCK	9	
4	A0004175700	CELLULAR (NON-KIT) 12V LC	1	
5	A0007504510	KIT - CUSTOMER CONNECTIONS	1	
6	0G3111	SCREW HHTT M6-1.0 X 25 ZINC	2	
7	A0008668800	KIT-CONTROLLER REPLACEMENT	1	
8	A0007504667	KIT-MOUNTING	1	
9	0K2098	RELAY 12V 30A SPST PILOT DUTY	2	
10	A0007261931	HARN AC HSB PZ200 SSI 60HZ 817/997 2BP	1	
11	A0008224796	PLUG BACK PANEL HSB RIBBED	2	
12	A0006221871	BATTERY POST COVER RED +	1	
13	0J6153	DECAL WARN THROUGH CONDUCTORS	1	
14	0J5765	DECAL SERVICE ENTRANCE WARNING	1	
15	A0004957116	HARN STATOR LEADS AC HSB 1P 254 8AWG	1	Item not shown
16	G00735230	KIT - BATTERY TRAY 30L	1	

Part No. A0009047391 Rev. E 08/04/2026
© 2026 Generac Power Systems, Inc.
All rights reserved.
Specifications are subject to change without notice.
No reproduction allowed in any form without prior written
consent from Generac Power Systems, Inc.



Generac Power Systems, Inc.
S45 W29290 Hwy. 59
Waukesha, WI 53189
1-888-GENERAC (1-888-436-3722)
www.generac.com