
GENERAC®

Parts Manual

GP3600 49ST/CSA

Model: G0077210



SAVE THIS MANUAL FOR FUTURE REFERENCE

This page intentionally left blank.

Table of Contents

Unit 6

Control Panel -10000034471 8


Engine 10

QUICK REFERENCE GUIDE		
Engine Size	**Fuel**	**Engine Part No.**
212CC	GASOLINE	A0013054376
QUICK REFERENCE PARTS		
Description	**Part No.**	**Special Notes**
SPARK PLUG	0J00620106	
FILTER, AIR	A0013054377	

THREADED FASTENER ASSEMBLY TORQUE		
Item	**Hardware**	**N-m [Lb-ft]**
Stator bolt	Bolt M6 x 160mm	8 ~ 12 [5.9 ~ 8.9]
Rotor bolt	Bolt M8 x 215mm	32 ~ 36 [23.6 ~ 26.6]
Fuel tank	Bolt M8 x 25mm	22 ~ 28 [16.2 ~ 20.7]
Ground wire assembly	Bolt M6 x 20mm	8 ~ 12 [5.9 ~ 8.9]
Muffler	Bolt M8x30mm	22 ~ 28 [16.2 ~ 20.7]
Muffler bracket to alternator	Bolt M8 x 16mm	22 ~ 28 [16.2 ~ 20.7]
Panel to frame	Bolt M8 x 40mm	8 ~ 10 [5.9 ~ 7.4]
Brush holder	Bolt M5 x 16 mm	1 ~ 3 [0.7 ~ 2.2]
AVR	Bolt M5 x 16 mm	1 ~ 3 [0.7 ~ 2.2]
Alternator end Cover	Bolt M5 x 16 mm	5 ~ 7 [3.7 ~ 5.2]]
Isolator nuts	Nut flange M8	22 ~ 28 [16.2 ~ 20.7]

This page intentionally left blank.


Unit


3
5
4
2
1
22
21
6
7
24
8
9
11
10
A
25
23
17
20
15
12
18
16
14
19
13
22
21
Detail A

Unit (continued)

Item	Part Number	Description	Qty.	Remarks
1	A0013054340	KIT-FUEL TANK 3.7 GAL	1	
2	A0011014605	KIT-TANK HARDWARE	4	
3	10000007721	FUEL CAP	1	
4	10000035980	FILTER-FUEL	1	
5	10000039066	GAUGE-FUEL	1	
6	A0010137766	FUEL COCK	1	
7	A0013054341	KIT-MUFFLER ASSEMBLY	1	
8	404031	GASKET,EX.PIPE,ENG,SB1,DR, 7HP	2	
9	10000034462	ALTERNATOR 3.4KW	1	
10	10000039034	REGULATOR-AUTOMATIC VOLTAGE	1	
11	A0008144722	BRUSH-ALTERNATOR	1	
12	A0013054342	KIT-CO SENSE MODULE	1	
13	A0013054343	KIT-FRONT CONTROL PANEL COVER	1	
14	A0013054344	KIT-BACK CONTROL PANEL COVER	1	
15	10000034471	ASSEMBLY CONTROL PANEL	1	SEE DETAIL VIEW FOR SERVICE PARTS
16	A0013054345	KIT-FRAME FOOT	2	
17	A0013054346	KIT-ENGINE ISOLATOR	4	
18	A0013054347	KIT-HANDLE ASSEMBLY	1	
19	A0013054348	KIT-WHEEL ASSEMBLY	2	
20	A0013054349	KIT-FRAME PANEL	1	
21	A0013054350	KIT-GAS FUEL HOSE	1	
22	A0013054351	KIT-FUEL TANK VENT LINE	1	
23	A0013054352	KIT-BOTTOM SHROUD	1	
24	0J5207C110	SPARK ARRESTOR MFG#213100-248	1	
25	A0013054376	ENGINE REPLACEMENT-212CC	1	


Control Panel -10000034471



Control Panel -10000034471 (continued)

Item	Part Number	Description	Qty.	Remarks
1	0G8321	HOUR METER W/ALERTS AC/DC	1	
2	A0000209995	SWITCH, ENGINE	1	
3	0G9392	COVER 20A 120V GFCI/DUPLEX	2	
4	0G9391	COVER 30A 120/240V	1	
5	10000038997	BREAKER-CIRCUIT 30A	1	
6	10000037725	RECEPTACLE (125V, 30A, RV)	1	
7	10000028117	GFCI RECEPTACLE (125V, 20A, DUPLEX)	2	
8	0H0265C	CB 20A 1P CUL/CSA	2	

Engine



Detail A

Engine (continued)

Item	Part Number	Description	Qty.	Remarks
1	A0013054353	KIT-CYLINDER HEAD COVER	1	
2	0J88870103	GASKET, HEAD COVER	1	
3	A0013054354	KIT-COIL ASSY, IGNITION	1	
4	0J00620106	SPARK PLUG	1	
5	A0013054355	KIT-SPRING GOVERNOR	1	
6	A0013054356	KIT- GOVERNER ARM	1	
7	A0013054357	KIT-THROTTLE HANDLE	1	
8	A0001393533	ASSEMBLY-DIPSTICK/CAP	1	
9	0J35220166	SEAL, OIL	2	
10	A0013054358	KIT-ALERT OIL PROTECTOR	1	
11	445841	BOLT , DRAIN PLUG ,SNW ENG,DR, 14HP	2	
12	0J35220164	WASHER, DRAIN PLUG	2	
13	A0013054359	KIT-HAND STARTER ASSY	1	
14	A0013054360	KIT- AIR FILTER	1	
15	A0013054377	AIR FILTER ELEMENT	1	
16	A0013054361	KIT-CARBURETOR	1	
17	403841	GASKET,CARBURETOR,ENG,SB1,DR, 7, 8HP	1	
18	403801	GASKET,CARB,ENG,SB1,DR, 7HP	1	
19	403821	GASKET,CARBURETOR,ENG,SB1,DR, 7HP	1	
20	A0013054362	KIT-AIR FILTER BRACKET	1	
21	10000039291	BREATHER TUBE	1	

Part No. 10000036615 Rev. C 10/09/2026
© 2026 Generac Power Systems, Inc.
All rights reserved.
Specifications are subject to change without notice.
No reproduction allowed in any form without prior written consent from Generac Power Systems, Inc.

Generac Power Systems, Inc.
S45 W29290 Hwy. 59
Waukesha, WI 53189
1–888–GENERAC (1–888–436–3722)
www.generac.com