


Parts Manual

GP7500E




SAVE THIS MANUAL FOR FUTURE REFERENCE

QUICK REFERENCE GUIDE		
Engine Size	Fuel	Engine Part No.
420CC	GASOLINE / LPG	A0011174490
QUICK REFERENCE PARTS		
Description	Part No.	Special Notes
PLUG, SPARK	A0003358923	
FILTER, AIR	A0011191641	
THREADED FASTENER ASSEMBLY TORQUE		
Item	Hardware	N-m [Lb-ft]
Stator Bolt	Bolt M6 x 195mm	8 ~ 12 [5.9 ~ 8.9]
Rotor Bolt	Bolt M10 x 1.25 x 283mm	25 ~ 30 [18.4 ~ 22.1]
Fuel Tank	Bolt M6 x 25mm	8 ~ 12 [5.9 ~ 8.9]
Ground Wire Assembly	Bolt M6 x 20mm	8 ~ 12 [5.9 ~ 8.9]
Muffler	Bolt M8 x 30mm	20 ~ 30 [14.8 ~ 22.1]
Muffler Bracket to Alternator	Bolt M8 x 16mm	20 ~ 30 [14.8 ~ 22.1]
Panel to Frame	Bolt M6 x 16 mm	6 ~ 10 [4.4 ~ 7.4]
Brush Holder	Bolt M5 x 16 mm	3 ~ 8 [2.2 ~ 5.9]
AVR	Bolt M5 x 16 mm	6 ~ 10 [4.4 ~ 7.4]
Alternator End Cover	Bolt M5 x 12 mm	6 ~ 10 [4.4 ~ 7.4]
Isolator Nuts	Nut Flange M10	20 ~ 30 [14.8 ~ 22.1]


This page intentionally left blank.

7.5KW G0080112 P1




7.5KW G0080112 P1 (continued)

Item	Part Number	Description	Qty.	Remarks
1	A0000121536	ASSY ALT 7800W AL/AL W/CTRL WINDING	1	
2	A0010526909	BRUSH	1	
3	0070672SRV	MODULE AVR 5.5KW TT09-3E LIHUA	1	
4	A0011174475	KIT-ENGINE ISOLATOR	1	
5	A0003084248	TUBE-NYLON BRAIDED	1	
6	A0011174476	KIT-EXHAUST PIPE	1	
7	10000004609	EXHAUST GASKET	2	
8	A0011174477	KIT-MUFFLER BRACKET	1	
9	A0011174478	KIT-WHEEL	1	
10	A0011174479	KIT-COVER SHROUD	1	
11	A0002433738	CONTROL PNL ASSY GP7500E DF CO2.5	1	
12	A0000420927	METER-HOUR	1	
13	10000004563	SWITCH ASSEMBLY	1	
14	A0000420930	BREAKER-CIRCUIT (20A)	2	
15	A0000420931	RECEPTACLE (5-20R 120V 20A GFCI)	2	
16	A0007117228	DUST COVER-CONTROL PANEL	2	
17	A0000420937	RECEPTACLE (L14-30R 120/240V 30A)	1	
18	A0003022705	COVER-DUST	1	
19	A0000444789	BREAKER, CIRCUIT	1	
20	A0003022765	SOCKET-CHARGING	1	
21	A0003081160	BATTERY	1	
22	A0011174480	KIT-HANDLE	1	
23	A0011174481	KIT-LOW PRESSURE HOSE	1	
24	A0011174482	KIT-REGULATOR	1	
25	A0011174483	KIT-FUEL SELECTOR SWITCH	1	
26	A0011174484	KIT-UNIT FEET	2	
27	A0008445848	CHARGER	1	
28	A0001482450	REGULATOR 1ST STAGE W/HOSE PM-DF	1	
29	A0011191639	CARBON CANISTER	1	
30	A0011174485	KIT-CO MODULE	1	
31	A0011174486	KIT-CARBON CANISTER HOSES	1	
32	A0011174487	KIT-BATTERY CABLES	1	
33	A0011174488	KIT-BATTERY BRACKET	1	
34	A0011174489	KIT-FUEL HOSE	1	
35	A0000177109	168 FUEL VALVE WITH FLAT GASKET	1	



7.5KW G0080112 P2 (continued)

Item	Part Number	Description	Qty.	Remarks
1	A0011191640	KIT-FUEL TANK	1	
2	A0003083748	CAP-FUEL	1	



7.5KW G0080112 P3 (continued)

Item	Part Number	Description	Qty.	Remarks
1	A0011174490	REPLACEMENT ENGINE 420CC G32	1	
2	A0011174491	KIT-OIL DRAIN PLUG	1	
3	10000004426	CYLINDER HEAD GASKET	1	
4	A0011174492	KIT-HEAD COVER	1	
5	10000002627	BREATHER TUBE	1	
6	A0011174493	KIT-SHROUD	1	
7	A0001088823	DIPSTICK	1	
8	A0011174494	KIT-OIL LEVEL SENSOR	1	
9	A0011174495	KIT-CARBURETOR	1	
10	A0011174496	GASKET	1	
11	A0011174497	GASKET	1	
12	A0011174498	GASKET	1	
13	A0011174499	KIT-LOW PRESSURE HOSE	1	
14	A0011174500	KIT-FUEL LINE W/ FILTER	1	
15	A0011174501	KIT-AIR FILTER ASSY	1	
16	A0011191641	AIR FILTER ELEMENT	1	
17	A0011191652	OIL SEAL	2	
18	A0011174502	KIT-SHROUD ASSY	1	
19	A0003358923	SPARK PLUG G32	1	
20	A0011174503	KIT-GOVERNOR ARM	1	
21	A0011174504	KIT-RECOIL STARTER	1	
22	A0011174505	KIT-SPRING GOVERNOR	1	
23	A0011174506	KIT-STARTER MOTOR	1	
24	A0011174507	KIT-IGNITION COIL	1	

Part No. A0005699985 Rev. A (Initial Release) 06/29/2026
© 2026 Generac Power Systems, Inc.
All rights reserved.
Specifications are subject to change without notice.
No reproduction allowed in any form without prior written
consent from Generac Power Systems, Inc.



Generac Power Systems, Inc.
S45 W29290 Hwy. 59
Waukesha, WI 53189
1-888-GENERAC (1-888-436-3722)
www.generac.com