

Commercial Power Washer



4200 psi - Model G006565-0 (49-State & Canada)
UPC: 696471065657

4200 psi - Model G006565-1 (50-State & Canada)
UPC: 696471086805



*Assembled in the USA using domestic and foreign parts

FEATURES

PRO-GRADE TRIPLEX PUMP

- Up to 4X longer life than axial cam pumps

POWERFUL GENERAC OHV ENGINE

- Delivers maximum cleaning performance and reliability

STEEL-REINFORCED HOSE

- Durable, non-marring hose will not leave scuff marks

FOLDING HANDLE

- For compact storage and transport

WELDED ROLL CAGE FRAME

- Protects components and provides gripping surfaces for easier lifting

BRASS QUICK CHANGE FITTINGS

- For faster connections

PRESSURE CONTROL VALVE

- For adjustable cleaning power

PROFESSIONAL SPRAY GUN

- Quick change connections, stabilizing side handle, molded grip, and easier-to-pull trigger for comfort during prolonged use

4200 psi**specifications****PRESSURE AND FLOW**

Max Outlet Pressure (psi/bar)	4200/290
Max Flow Rate (gpm)/(L/min)	4.0/15.1

ENGINE

Manufacturer	Generac
Displacement (in ³ /cc)	25.6/420
Type	OHV (Overhead Valve)
Orientation	Horizontal
Low Oil Shutdown System	Yes
Fuel Capacity (gal/L)	1.7/6.5
Fuel On/Off Switch	Yes
Oil Capacity (oz/L)	37/1.1
Recommended Engine Oil	10W-30/SAE 30
Throttle Control	Manual
Choke	Manual
Starting Method	Manual/Recoil Pull Start

PUMP

Type	Triplex
Plunger	Ceramic-coated Stainless Steel
Maximum Water Supply Temperature (°F/°C)	100/38

HOSE

Length (ft/m)	50/15.2
Rating (psi/bar)	4200/290
Connectors	Quick Change

NOZZLES

Number of Nozzles per Unit	5
Nozzle Descriptions	0°, 15°, 25°, 40°, Soap

GUN & LANCE

Gun Type	Professional
Gun to Lance Connection	Quick Change
Gun to Hose Connection	Quick Change
Lance Length (in/cm)	33/84
Lance to Nozzle Connection	Quick Change

FRAME & MISC.

Handle	Folding
Frame Construction	Welded Steel
Wheels (in/cm)	4 x 12/10.2 x 30.5 Pneumatic

DIMENSIONS & WEIGHTS

Length (in/cm)	34.5/87.6
Width (wheel to wheel, in/cm)	28.3/71.8
Height (in/cm)	42.5/108
Unit Weight (lbs/kg)	146.5/66.5
Boxed Length (in/cm)	29/73.7
Boxed Width (in/cm)	28/71.1
Boxed Height (in/cm)	33.5/85.1
Boxed Weight (lb/kg)	164/74.4

WARRANTY

Warranty	3 Year Limited
----------	----------------