


GROUP A



EXPLODED VIEW: EV ALTCOMPRTS G4.5L C3

DRAWING #: A0000277555

GROUP A

ITEM	PART#	QTY.	DESCRIPTION
(2)1	0A8258	6	SCREW HHC M8-1.25 X 25 C10.9
2	G022129	6	WASHER LOCK M8-5/16
(2)3	0A2601	1	SCREW HHC M16-2.0 X 45 C8.8
4	0G0724	1	FAN MACHINED 390 SAE ALTERNATOR
5	0A1138	1	KEY SQ 3/8 X 2-1/2 STEEL
6	A0000100190	1	COUPLER 390 SAE PD
7	A0000276973	1	RTR 390 60KW BRUSHLESS CPL 2019
	A0000221228	1	RTR 390 80KW BRUSHLESS CPL 2019
(1) 8	G052624	1	BEARING BALL 6212 SEALED
9	G072878	1	KEY SQ 3/8 X 3-1/4 STEEL
10	G043123	4	WASHER LOCK M14
11	A0000276975	1	STR 390 60AB1 PROT GAS 2019 (RG,HG)
	A0000276986	1	STR 390 60GB1 PROT GAS 2019 (RG,HG)
	A0000330292	1	STR 390 60JB1 PROT GAS 2019 (RG,HG)
	A0000330297	1	STR 390 60KB1 PROT GAS 2019 (RG,HG)
	A0000222710	1	STR 390 80AB1 CPL 2019 (RG,HG)
	A0000262450	1	STR 390 80GB1 PROT GAS 2019 (RG,HG)
	A0000330302	1	STR 390 80JB1 PROT GAS 2019 (RG,HG)
	A0000330304	1	STR 390 80KB1 PROT GAS 2019 (RG,HG)
	A0007646034	1	STR 390 60AB1 CPL 2025 (XG)
	A0007630492	1	STR 390 60KB1 CPL 2025 (XG)
	A0007176662	1	STR 390 80AB1 CPL 2025 (XG)
	A0007160726	1	STR 390 80KB1 CPL GAS 2025 (XG)
12	G068113	1	CARRIER REAR BRG 15"
13	A0000204424	4	STUD M14-2.0 X 700
14	G052646	4	WASHER FLAT M14
15	G051779	4	NUT HEX M14-2.0 G8 YEL CHR
16	G052259	2	WASHER FLAT M12
17	G051769	9	WASHER LOCK M12
18	G067052	1	SCREW HHC M12-1.75 X 70 C8.8
19	A0005636495	2	DEFLECTOR SCROLL
20	G087272	1	ASSY EXCITER 2.00" STK
21	068405C	1	EXITER FIELD 2" LG SPD CONN
22	0H7625E	1	COLLAR SLIP FIT 43.91MM
23	0A2602	1	WASHER FLAT .688ID X 3.25OD
24	G022392	2	PIN DOWEL 1/2 X 1-1/4
25	G090063	1	BRIDGE SUPPORT DIODE 15"
26	G090152	1	ASSY BRIDGE RECTIFIER
27	G023365	2	WASHER SHAKEPROOF INT #8
28	G033143	2	SCREW HHM #8-32 X 7/8
29	G090064	1	CAP END ROTOR 390MM
30	G063837	6	SCREW HHC M12-1.75 X 30 C10.9
31	G049808	6	WASHER FLAT M12
32	G022145	6	WASHER FLAT 5/16-M8 ZINC
33	0A8240	2	FLEX PLATE SAE10
34	0D3700	4	NUT FLANGE M6-1.0 NYLOK
35	G049721	4	SCREW HHC M6-1.0 X 35 C8.8 CLR
36	0K18270ST03	2	SCROL 390 ALTERNATOR
37	G022473	4	WASHER FLAT 1/4-M6 ZINC
38	G055597	REF	SCREW HHC M12-1.75 X 85 C8.8
39	G052259	REF	WASHER FLAT M12
40	G052252	REF	DAMPER VIBRATION
41	G052257	REF	SPACER .49X.62X1.87 PWDR/ZINC
42	A0000302928	REF	DAMPER VIB 60 DURO
43	G052860	REF	NUT TOP LOCK FL M12-1.75
44	G033133	1	SCREW HHM #8-32 X 3/8
45	G020151	1	CLAMP STL/VNL .312 X .203
46	0E7230	2	SCREW HHC M12-1.75 X 80 C10.9

NOTES (UNLESS OTHERWISE SPECIFIED):

(1) ROTOR REPLACEMENT PART

(2) APPLY MEDIUM STRENGTH BLUE THREAD LOCKING FLUID TO THREADS.

(3) TORQUE VALUES: (FOR REFERENCE ONLY)

ITEM #15 - 102 ft-lbs.

ITEM #3 - 123 ft-lbs.

ITEM #1 - 20 ft-lbs.

(4) ALL STANDARD HARDWARE TO BE TORQUED PER EDS001.